

Configured Valve Trains

Model VT03 (3/4" N.P.T.)

Version 1

The Eclipse configured valve trains use a variety of shut-off valves, regulators, and associated components. These valve trains are rated for 110-120V / 50-60 Hz operation and are designed to meet the requirements of NFPA 86 - 2003 or Industrial Risk Insures (IRI) IM.4.2.0. The IRI version includes either a vent valve or a valve proving system. Standard components of all valve train sizes include safety shut-off valves, manual shut-off valves, high & low pressure switches, visual position indicators and pressure taps for valve seat leak testing and in-line strainers. Optional components consist of regulators, valve leak test systems, upstream and downstream gauges (21/2" face diameter) and pilot gas trains (1/2" or 3/8").

A standard configured valve train ordered with or without an agency designation does not guarantee compliance or noncompliance with the standard. The end-use application for the valve train determines any additional requirements to meet full compliance to the standards such as:

- Some components may require vent lines to a safe outside location.
- The customer gas supply shall have an isolation valve followed by a vertical drip leg of 3 pipe diameters but not less than 3".
- Also, external control devices may be used to meet the requirements of a standard. In this case, the valve train may need to be ordered with option X for NONE under Agency Approval to allow the most versatility in selection of component options.

		Max.		Agency			ıcy	,		
Component***	Enclosure Rating (NEMA)	Operating Pressure PSI	Temperature Limits °F	l L	U L R	S	F	CE	Comments	
ASCO 8214 Valves	I	5	-40 to 125	• • •			Aluminum Body			
Dungs Dual Block Valve	1 & 12	7	-40 to 150			•	Aluminum Body			
Siemens VGG w/ SKP Actuators	1,2,5 & 12	20	15 to 140	•	• • •			Aluminum Body		
Manual Shut Off Valves	N/A	600	-40 to 366	•	• • •			Brass w/ teflon seals		
Pressure Switches*	1,4 & 12	7	-40 to 140	•	• • •			Auto or Manual Reset		
Vent Valve (3/4")	1,2,3,3S,4 & 4X	5	-40 to 125	•	• •			Aluminum Body		
Valve Proving System (VDK)	12	5	15 to 140		•	•	•		Aluminum Housing	
Valve Proving System (VPS)	12	7	5 to 140		Aluminum Hou		Aluminum Housing			
Pressure Regulator (Sensus)**	N/A	15, 125, 150	-20 to 150		Cas			Cast Iron Body		
Pressure Regulator (FRI)	N/A	7	5 to 160		•	•	•		Aluminum Housing	

^{*} Switches for 40"-200" w.c. are rated for 14 psi max. and -22°F to 140°F.




^{**} Operating Pressure depends on Model selected.


^{***} Refer to manufacturer's data sheets for specific component details.

Dimensions & Specifications


ASCO Safety Shut Off Valves



Dungs Dual Modular Shut Off Valve



Siemens Shut Off Valves




When using the Siemens SKP20 and SKP70 actuators for pressure regulating and ratio regulating functions, the sensing piping is not included. For proper operation, the sensing pipe should be at least 1/4" I.D. and connected a minimum of 5 pipe diameters downstream in a non-turbulent area. WARNING: For proper and safe operation, the installer must read and thoroughly understand the Siemens Technical Instructions 155-514P25 for the SKP20 and 155-516P25 for the SKP70.

Dimensions & Specifications (Continued)

3/4" N.P.T. Valve Train	Overall	Length	Δ P ("w.c.) through (2) Safety Shut-off Valves	Enclosure Rating	Temperature	SSOV Maximum Operating Pressure (PSI)**	
Arrangements	Minimum	Maximum	@ 560 scfh	(NEMA)	Range (° F)		
ASCO NFPA	938 mm (36.9")	1054 mm (41.5")	1.65	1	-20 to 125	5	
ASCO IRI* w/ Vent Valve	1053 mm (41.5")	1169 mm (46.0")	1.65	1	-20 to 125	5	
Dungs Dual NFPA	434 mm (17.1")	484 mm (19.1")	1.6	12	5 to 140	7	
Dungs Dual IRI	434 mm (17.1")	484 mm (19.1")	1.6	1	5 to 140	7	
Siemens NFPA	906 mm (35.7")	1022 mm (40.2")	1.6	12	15 to 140	7	
Siemens IRI w/ Vent Valve	1021 mm (40.2")	1137 mm (44.7")	1.6	12	15 to 140	5	

^{*}ASCO IRI with valve proving system differs with a temperature range of 15° to 125° F, and a shorter overall length.

Capacities



^{**} Depends on components selected, pressure switches. etc.



Offered By:
Power Equipment Company
2011 Williamsburg Road
Richmond, Virginia 23231
Phone (804) 236-3800 Fax (804) 236-3882